



# 5210 siacarat microtec



Zrno:  
diamant

100 μ	
80 μ	
<b>60 μ</b>	●
50 μ	
<b>45 μ</b>	●
40 μ	
<b>30 μ</b>	●
20 μ	
<b>15 μ</b>	●
12 μ	
<b>9 μ</b>	●
6 μ	
5 μ	
3 μ	
1 μ	
0,5 μ	
0,1 μ	



Posyp:  
speciální, lesklý



holý

SKF

100 μ		
80 μ		
<b>60 μ</b>	●	●
50 μ		
<b>45 μ</b>	●	●
40 μ		
<b>30 μ</b>	●	●
20 μ		
<b>15 μ</b>	●	●
12 μ		
<b>9 μ</b>	●	●
6 μ		
5 μ		
3 μ		
1 μ		
0,5 μ		
0,1 μ		

Podklad:  
speciální fólie 75 μm

